



## AIR SHOWER BASB-103

## AIR SHOWER BASB-103

Air shower is a necessary passage for people entering clean room in order to minimize the amount of particulate contaminant, to achieve workplace strict clean purification standards Personnel move through the air shower while particulate contaminants are blown off by the clean high-speed air. Then the dust cannot be brought into clean air Used in Laboratory, Microbiological, Research ,University ,.

Also known as Personal Cleaning Booth.

## BASB-103 AIR SHOWER



Photoelectric sensor, automatic blowing

Adopt with circulation wind to ensure the cleanness of shower area under non-shower status

Double door by electric interlock

LED display with adjustable blowing time (0-99s)

HEPA filter, Class 100 cleanness

## SPECIFICATIONS

Model	BASB-103
External Size (WxDxH)	1500x2000x2050 mm
Internal Size (WxDxH)	800x1900x1930 mm
HEPA filter	99.995 % efficiency at 0.3 $\mu$ m
Spraying Wind Speed	25 m/s
Air Shower time	0-99 s (adjustable)
No. of SS Nozzels	24
Fluorescent Lamp	12Wx1
Consumption	2200 W
Cabinet Material (Optional)	1.Full cold-rolled steel with powder coating 2.Internal stainless steel, external with cold-rolled steel (optional) 3.Full stainless steel (optional)
Door Material (Optional)	1.Cold-rolled steel with powder coating 2.Stainless steel (optional)
Chassis	Stainless Steel
Power Supply	AC220 V $\pm$ 10%,50/60 Hz ; 110 V $\pm$ 10%, 60 Hz
Gross Weight	700 kg
Package Size (WxDxH)	1600x2200x2200 mm



**Biolab Scientific Ltd.**

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)