



MUFFLE BOX FURNACE BFMF-1100-20B

MUFFLE BOX FURNACE BFMF-1100-20B

Designed for minimum space requirements, our muffle furnaces work effortlessly at high temperatures and give reliable results. Equipped with electronic controller and memory to store different programs, it makes the operation user friendly. Chambers are crafted for heavy duty operation and minimize heat loss.

Used in Ideal for material testing, ashing, annealing loss determination, chemical analysis, reaction studies, metallurgical research and rapid heat processes..

BFMF-1100-20B MUFFLE BOX FURNACE



Programming with Easy-to-Understand Menu on 4-Line LCD Display

Suitable for all Kinds of Processes such as Ash Analysis, Heat Treatment, Sintering, Preheating, Melting, Oxidation

Durable Inner Chamber Made of Light Isolation Bricks

Accurate Measurement and Temperature Control with K Type Thermocouple

Homogeneous Heat Distribution

Space-Saving in the Laboratory with Unique Insulation Design

Low External Surface Temperature with Dual Layer Housing

Heating Elements which are Selected and Designed According to Their Proper Working Temperatures and Providing Fast Heating of the Furnace

Heating Element Protection with Quartz Tubes against the Effects of Harmful Gases

Fan and Chimney System for Discharging Corrosive and Oxidizing Gases

Optional Features such as Protective Gas Connection, Door Sensor, Second Thermocouple (Indicator)

Lift-Up & Sideways Door Options

SPECIFICATIONS

Model	BFMF-1100-20B
Capacity	20 L
Maximum Temperature	1100°C
Working Temperature	1100°C
Control Unit	B2
Controller Description	4x20 LCD / 4 Steps 2 Prog
Software Options	B2, E4, U8, S16
Control Accuracy	±1°C
Front Face Insulation Material	Ceramic Fire Brick
Door Insulation Material	Ceramic Fibre Board
Housing Material	Steel Sheet
Housing Coating	Epoxy Powder Coating
Chimney	Standard
Heating Element Protection	Quartz Tube
Lockable Door Handle	Sideways
Inner Insulation Material	Insulating Fire Brick
Heating Element Placement	Embedded into Brick Walls
Thermocouple Type	K Type
Heating Element Type	Fe-Cr-Al
Inner Dimension (WxDxH)	250x200x395 mm
Outer Dimension (WxDxH)	546x668x790 mm

Gross Dimensions (WxDxH)	606x950x728 mm
Net Weight	65 Kg
Gross Weight	85 Kg
Power	4200 W
Maximum Current	2×9.6 / 1×19.1 A
Electrical Connection	3 vey a 1 Phase
Power Supply	220V / 50Hz
Note	Available model with capacity 7L, 10L, 40L, 60L



Biolab Scientific Ltd.

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com