



STANDARD FUME HOOD BFSD-303

STANDARD FUME HOOD BFSD-303

Designed to provide personnel protection from toxic fumes and hazardous volatile vapours, our standard fume hoods are reliable and easy to use. Its inbuilt ventilation system with a front window eliminates fire and explosion risk. Acid\alkali resistant interiors and UV lamp to sterilise the work area, this product is the best choice for reducing potential exposure hazard to the user.

Used in Metal analysis, Pharmacy, Research Field, Commercial, Medical, Laboratory.

Also known as Standard Fume Hood, Laboratory Fume Hood, Chemical Fume Hood.

BFSD-303 STANDARD FUME HOOD



Adjustable air speed: 9 levels

Microprocessor control system, LED display

With memory function in case of power-failure

Manual front glass window, height adjustable

Built-in PP centrifugal blower; low noise, easy installation

Exterior material: 1.0 mm cold-rolled steel with bacteria powder coating

Interior material: High grade melamine board with moderate acid and alkali resistance

Work table material: Chemical resistant phenolic resin

SPECIFICATIONS

Model	BFSD-303
Air Velocity	0.3~0.8 m/s
System Exhaust Volume	930 m³/h
Max Opening	750 mm
Exterior Material	1.0 mm cold-rolled steel with bacteria power coating
Interior Material	Compact material board with good acid and alkali resistance function
Work Table Material	Chemical resistant Phenolic resin
LED Lamp	40Wx1
Front Window	Manual, 5 mm toughened glass; height adjustable
Exhaust Duct	PVC, Standard length; 4.3 meters, ϕ 300 mm
Blower	Built-in PP centrifugal blowers
Standard Accessory	PP Water Sink, Total load of 2 waterproof socket: 500 W Base Cabinet, Water tap 4 meters PVC exhaust duct (ϕ 300mm), Pipe Strap - 2 pcs
Optional Accessory	Air Supply flow control valve, gas faucet
Work Surface Height	900 mm
Internal Size (WxDxH)	1290x600x870 mm
External Size (WxDxH)	1500x800x2515 mm
Package (Main Body)	1640x940x1900 mm
Package Size (Base Cabinet)	1940x940x1050 mm
Noise Level	\leq 68 dB
Gross Weight	335 kg
Consumption	500 W
Power Supply	222V \pm 10%, 60/50Hz; 110V \pm 10%, 60Hz



Biolab Scientific Ltd.

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com