



STANDARD FUME HOOD BFSD-401

STANDARD FUME HOOD BFSD-401

Designed to provide personnel protection from toxic fumes and hazardous volatile vapours, our standard fume hoods are reliable and easy to use. Its inbuilt ventilation system with a front window eliminates fire and explosion risk. Acid\alkali resistant interiors and UV lamp to sterilise the work area, this product is the best choice for reducing potential exposure hazard to the user.

Used in Metal analysis, Pharmacy, Research Field, Commercial, Medical, Laboratory.

Also known as Standard Fume Hood, Laboratory Fume Hood, Chemical Fume Hood.

BFSD-401 STANDARD FUME HOOD



Microprocessor control system, LED display

Made of porcelain white PP, Resistant to acid, alkali and anti-corrosion

With memory function in case of power-failure

Manual front glass window, height adjustable

Built-in PP centrifugal blower; low noise, easy installation

Chemical resistant phenolic resin work table

Optional: PP work table, epoxy resin board or ceramic board

SPECIFICATIONS

| | |
|-----------------------------|---|
| Model | BFSD-401 |
| Air Velocity | 0.3~0.8 m/s |
| Max Opening | 740 mm |
| Work Surface Height | 820 mm |
| Exhaust Duct | 4.3 meters, ϕ 250 mm |
| LED Lamp | 12Wx2 |
| Front Window | Resistant to acid and alkali, Manual, 5 mm toughened glass, height adjustable |
| Blower | Built-in PP centrifugal blowers, speed adjustable |
| Work Table Material | Chemical resistant Phenolic resin |
| Standard Accessory | LED light; Work table: Chemical resistant Phenolic resin; 4.3 meter PVC duct, Diameter: 250 mm pipe strap x2, RVV power cord (3x1.0 mm ² x 3000mm), Base cabinet, Waterproof socket x2, Tail insert, Water tap (PP), Gas tap (PP), Water sink, PP centrifugal blower x 1 |
| Optional Accessory | PP work table, epoxy resin board or ceramic board; Active carbon filter; outer PP centrifugal blower x1, Splicable base cabinet |
| Internal Size (WxDxH) | 787x560x700 mm |
| External Size (WxDxH) | 1047x800x2450 mm |
| Package (Main Body) | 1188x938x1612 mm |
| Package Size (Base Cabinet) | 1188x888x1000 mm or 1200x1000x450 mm |
| Noise Level | \leq 68 dB |
| Gross Weight | 137 kg (Main body) 89 kg or 80 kg (Base Cabinet) |
| Consumption | 400 W |
| Power Supply | AC220V \pm 10%, 60/50Hz; 110V \pm 10%, 60Hz |



Biolab Scientific Ltd.

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com